


## Pre-made Pouch Filler / Sealer for Large Pouches

# TT-8A2




- Widely flexible for various pouch formats and product types.
- Designed for safe and sanitary operation.
- Easy clean design.
- Simple, intuitive operation and maintenance using touch screen controls.
- Optional zipper opening, nitrogen gas flush, liquid filling systems and other features.



Stations



Simplex





### DDS1 - Synchronized Following Funnel

(Option) Continuous following funnels provide up to 50% more filling time. Increase throughput on challenging products and large volume products.





### HMI: Color Touch Screens

User-friendly, information rich screens with maintenance functions.

## Machine Dimensions

\* Specifications & dimensions subject to change without notice



## Machine Specifications

\* Depending on product

<b>Capacity</b>	max. 50 ppm
<b>Pouch Size</b>	W: 180 - 320 mm L: 140 - 400 mm
<b>Pouch Material</b>	Various laminated pouches, PE pouch
<b>Pouch Style</b>	Flat, standup & floating gusset. Optional ptc zipper style.
<b>Sealing Method</b>	2-stage heat/cool sealing method
<b>Electric Power</b>	6.5 kVA
<b>Air Consumption</b>	0.6MPa (72psi), 600 NL/min(ANR)
<b>Machine Dimension &amp; Weight</b>	W 2,250 x L 3,900 x H 1,900 mm 2,100Kg
<b>Accessories</b>	Air grippers, Product feeding hopper Product discharge conveyor, Product counter Pouch handling vacuum pumps, Pouch recycle Pouch opening following guide Heater disconnection alarm
<b>Options</b>	Date printer, Air squeeze device, Tapping Stand-up pouch bottom opening device N2 Gas flush device, Zip open-close device Various filling devices, Pouch pick-up position detection Product in seal detection, Dust collecting device Synchronized following funnel (DDS1) Adjustable gripper height device (AGH)

## Applications

Snacks, Rice & other grains, Pet foods, Frozen foods  
Granular & powder products and many others